

Pressalit Calmo® with soft close, incl. BZ5 fixed hinge  
Pressalit Calmo® with soft close, incl. D15 universal hinge  
Pressalit Calmo® with soft close and lift-off, incl. D72 universal hinge

No. 556xxx-BZ5999 with cover  
No. 556xxx-D15999 with cover  
No. 556xxx-D72999 with cover



**Design/Year**

Pressalit, 2007, registered trademark and design

**Product Description**

PRESSALIT toilet seat with cover, model "Calmo", art. no. 556 made of colour ingrained duroplast with stainless steel hinges.

- with BZ5 fixed hinge, D15/D72 universal hinge of stainless steel.
- centre distance:  
BZ5: 155 mm, D15/D72: 133-215 mm.
- load - ring seat 240 kg.
- suitable for universal toilets.
- 10 year guarantee.

**Colour Programme xxx**

000 white, 001 black,  
052 manhattan, 273 pergamon

**Alternative Hinge**

D01 Universal top mounted hinge  
D02 Universal flex toggle hinge  
D73 Universal top mounted hinge with lift-off  
D69 Universal flex toggle hinge with lift-off


**Hinge Finish**

999 Stainless steel


**Spare Parts**

A4030 Buffer for cover, grey  
A4001 Buffer for seat, grey


**BZ5**




**BZ5**




**D15**





**D15**



**D72**



**D72**



Say goodbye to slamming seats. And welcome to Calmo - the calm luxury in everyday life.  
A seat with minimalistic and pure lines where soft close is taken for granted.

Pressalit Calmo® with soft close, incl. BZ5 fixed hinge  
Pressalit Calmo® with soft close, incl. D15 universal hinge  
Pressalit Calmo® with soft close and lift-off, incl. D72 universal hinge

No. 556xxx-BZ5999 with cover  
No. 556xxx-D15999 with cover  
No. 556xxx-D72999 with cover

#### Product Weight

Net weight approx. 3,100 kg incl. BZ5 hinge  
Net weight approx. 3,000 kg incl. D15/D72 hinge

#### Packaging

Single carton incl. BZ5 hinge	Dimensions: 463x385x75 mm	Weight: 3,300 kg
5 single cartons in a master carton	474x392x395 mm	17,700 kg
12 master cartons (60) per pallet		
Single carton incl. D15/D72 hinge	Dimensions: 463x385x75 mm	Weight: 3,400 kg
5 single cartons in a master carton	474x392x395 mm	17,700 kg
12 master cartons (60) per pallet		

#### Material Description

##### Toilet seat:

The material is colour ingrained duroplast (UF A 10=urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.

##### Buffers:

EVA (copolymer made of ethylene and vinyl acetate).

##### Damper kit:

Hydraulic damper with plastic casing and metal shaft.  
Damper liquid: Silicone oil.

##### Mount/hinges:

Stainless steel ASTM A351 grade CF-8.  
Composition: chrome (cr) 18-21%, nickel (ni) 8-11%, carbon <0.08%, molybdenum, silicone, sulphur, titanium.

##### Konsol:

Acid proof stainless steel type EN 1.404/A1S1 316L  
Composition: chrome (cr) 16,5-18,5%, nickel (ni) 10-13%, molybdenum 2-2,5% , mangan, silicone, sulphur, titanium.

#### Suitability List

Usable on universal toilets – see [www.pressalit.com](http://www.pressalit.com)

#### Cleaning Instructions

Use a mild soap solution to clean the seat. Please take care that the seat and hinges are not left damp. Dry off any residual water or cleaning agent with a soft cloth. Avoid contact of the seat and hinges with abrasive, corrosive or chlorine-based cleaners, as these may cause damage or lead to flash rust. Therefore, when cleaning the bowl, make sure that the seat and cover are kept in an upright position until all cleaning agent has been flushed away.



Pressalit A/S, Denmark



The guarantee includes faults or defects in the material of our products within a period of 10 years.  
Products subject to minor technical modifications and design deviations E. & O.E.

[www.pressalit.com](http://www.pressalit.com)

European Sales Agencies  
Leith House, 39 Campion Drive  
Tanfield Lea, Stanley  
Co Durham, DH9 9PQ, United Kingdom  
T: +44 1207 236622  
F: +44 1207 236633  
[info@europeansalesagencies.com](mailto:info@europeansalesagencies.com)  
[www.europeansalesagencies.com](http://www.europeansalesagencies.com)

Pressalit A/S  
Pressalitvej 1  
8680 Ry, Denmark  
T: +45 8788 8788  
F: +45 8788 8789  
[pressalit@pressalit.com](mailto:pressalit@pressalit.com)  
[www.pressalit.com](http://www.pressalit.com)

**PRESSALIT®**  
seats