

Pressalit New Scandinavia® with soft close,  
incl. BP9 universal hinge with quick-release

No. 472xxx-BP9999  
with cover




Design/year

Pressalit, 2005, registered trade mark and design

Product Description


PRESSALIT toilet seat with cover, model "New Scandinavia", art. no. 472 made of colour ingrained duroplast with soft close, incl. hinge link in chromium-coated zinc, quick-release universal hinge in stainless steel and glass reinforced polyamide

- incl. BP9 quick-release universal hinge
- dismantling of seat/cover makes cleaning easier
- centre distance: 130 - 220 mm
- timeless design with rounded edges
- load - ring seat 240 kg
- soft close
- suitable for many universal toilets
- 10 year guarantee



Colour Programme xxx

000 white, 001 black, 004 moss green, 013 bahamabeige, 035 red, 046 yellow, 052 manhattan, 058 sorrento blue, 068 bermuda blue, 112 grey, 125 sunset, 143 caramel, 188 blue, 155 flame, 273 pergamon, 329 dark purple, 335 hot pink, 338 midnight blue




Hinge Finish

999 Stainless steel

Alternative Hinge

BQ7 Universal toggle hinge with quick-release



Spare Parts

A4023 Buffer for pushing into cover, oval, grey  
A4033 Buffer for pushing into seat, oval, grey  
A9172 Release button and spring



*Recognize the lines? No wonder, for it's like seeing time smile at you. A rendezvous between the past and the future. Classic form in new interpretation. The lines are attractive. The front is smiling. And why shouldn't it! The seat - with quick release and soft close - is designed to suit most new toilets, including the popular D-shaped pans.*

Product Weight

Net weight approx. 2,700 kg, incl. hinge

Packaging

Single carton  
5 single cartons in a master carton  
18 master cartons (90 seats) per pallet

Dimensions:

449x381x64 mm  
456x388x340 mm

Weight:

2,900 kg  
15,000 kg

Material Description

**Toilet seat:**

The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.

**Buffers:**

EVA (copolymer made of ethylene and vinyl acetate).

**Hinge links:**

Chromium-coated zinc in Zamak 5 type ZnAl4Cu1 in accordance with EN1774  
Surface coating: Copper (Cu), nickel (Ni), chromium (Cr)  
Hydraulic damper polycarbonate PC  
Release button SEBS/SBS  
Hinge link bush polyacetal POM

**Mount/hinges:**

QR pin and cover cap in stainless steel (V2A) type W.nr.1.4301/M in accordance with DIN 17441/85. Adjusting washer in 50% glass reinforced polyamide (nylon) Grivory GV-5H.  
Integrated washer in TPU.

Suitability List

Usable on universal toilets - see [www.pressalit.com](http://www.pressalit.com)

Cleaning Instructions

Use a mild soap solution to clean the seat. Please take care that the seat and hinges are not left damp. Dry off any residual water or cleaning agent with a soft cloth. Avoid contact of the seat and hinges with abrasive, corrosive or chlorine-based cleaners, as these may cause damage or lead to flash rust. Therefore, when cleaning the bowl, make sure that the seat and cover are kept in an upright position until all cleaning agent has been flushed away.

The guarantee includes faults or defects in the material of our products within a period of 10 years. Products subject to minor technical modifications and design deviations E. & O.E.



Pressalit A/S, Denmark



[www.pressalit.com](http://www.pressalit.com)