

Pressalit ConCordia® with soft close,
incl. D05 universal hinge with lift-off

No. 544xxx-D05999 with cover



Design/Year

Pressalit, 2007, registered trade mark and design

Product Description

PRESSALIT toilet seat with cover, model "ConCordia", art. no. 544 made of colour ingrained duroplast with stainless steel hinges with lift-off

- with D05 universal hinge of stainless steel with lift-off
- centre distance: 132 - 215 mm
- load - ring seat 240 kg
- suitable for many universal toilets
- 10 year guarantee

Colour Programme xxx

000 white, 001 black, 273 pergamon

Alternative hinge




BL6 Universal toggle hinge with lift-off

Hinge Finish

999 Stainless steel

Spare Parts

A4051 Delta buffer



The design of the Pressalit ConCordia is inspired by the Concorde airplane. A modern and classic seat that elegantly integrates the soft close and lift-off functions in the design. Suitable for a large number of toilet pans.

Pressalit ConCordia® with soft close,
incl. D05 universal hinge with lift-off

No. 544xxx-D05999 with cover

Product Weight

Net weight approx. 2,900 kg, incl. hinge

Packaging

Single carton
5 single cartons in a master carton
12 master cartons (60) per pallet

Dimensions:

463x385x75 mm
474x392x395 mm

Weight:

3,300 kg
17,200 kg

Material Description

Toilet seat:

The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. UF plastic comprises 67% urea formaldehyde resin, 28% cellulose, as well as 5% minerals, pigments, lubricants and moisture content. The raw material from the supplier contains up to 0.03% free formaldehyde and even less following curing.

Buffers:

EVA (copolymer made of ethylene and vinyl acetate).

Damper kit:

Hydraulic damper with stainless steel damper casing and thermoplastic parts.
Damper liquid: Anti-friction liquid.

Mount/hinges:

Stainless steel (V2A) model W. no. 1.4301/M in accordance with DIN 17441/85.

Composition: chrome (cr) 17-19%, nickel (ni) 8-11%, carbon <0.05%, molybdenum, silicone, sulphur, titanium.

Suitability List

Usable on universal toilets - see www.pressalit.com

Cleaning Instructions

Use a mild soap solution to clean the seat. Please take care that the seat and hinges are not left damp. Dry off any residual water or cleaning agent with a soft cloth. Avoid contact of the seat and hinges with abrasive, corrosive or chlorine-based cleaners, as these may cause damage or lead to flash rust. Therefore, when cleaning the bowl, make sure that the seat and cover are kept in an upright position until all cleaning agent has been flushed away.

The guarantee includes faults or defects in the material of our products within a period of 10 years.
Products subject to minor technical modifications and design deviations E. & O.E.



Pressalit A/S, Denmark



www.pressalit.com

European Sales Agencies
Unit 10c Tanfield Lea (North) Industrial Estate
Tanfield Lea, Stanley
Co Durham, DH99UU
Tel. 01207 236622, Fax 01207 236633
info@europeansalesagencies.com
www.europeansalesagencies.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel. (+45) 8788 8788
Fax (+45) 8788 8789
pressalit@pressalit.com

PRESSALIT®
seats