

Pressalit Delight® with soft close, incl. D09 universal flex hinge  
Pressalit Delight® with soft close and lift-off, incl. D78 universal flex hinge  
Pressalit Delight® incl. D09 universal flex hinge

No. 492xxx-D09999 with cover  
No. 492xxx-D78999 with cover  
No. 592xxx-D09999 with cover



**Design/Year**

Pressalit, 2007, registered trade mark

**Product Description**

PRESSALIT toilet seat with cover, model "Delight", art. no. 492/592 made of colour ingrained duroplast with hinges of stainless steel and plastic

- with D09/D78 universal flex hinge of stainless steel and plastic
- centre distance: 135-215 mm
- load - ring seat 240 kg
- suitable for D-shaped toilets
- 10 year guarantee

**Colour Programme xxx**

000 White, 001 Black

**Alternative Hinge**


- D01 Universal top mounted hinge
- D02 Universal Flex-toogle hinge
- D73 Universal top mounted hinge with lift-off
- D69 Universal Flex-toogle hinge with lift-off

**Hinge Finish**

999 Stainless steel and plastic

**Spare Parts**

- A4011 Buffer for pushing into seat, oval, grey
- A4030 Buffer for pushing into cover, round, grey



*Discrete. Design. Delicious. It is that simple to describe Delight. Literally speaking, Delight values the D and fits most of the D-shaped pans. Wrap-over underlines the stringent design. The seat is available with or without soft close.*

Pressalit Delight® with soft close, incl. D09 universal flex hinge  
Pressalit Delight® with soft close and lift-off, incl. D78 universal flex hinge  
Pressalit Delight® incl. D09 universal flex hinge

No. 492xxx-D09999 with cover  
No. 492xxx-D78999 with cover  
No. 592xxx-D09999 with cover

#### Product Weight

Net weight approx. 3300 gr., incl. hinge

#### Packaging

Single carton  
5 single cartons in a master carton  
12 master cartons (60) per pallet

#### Dimensions:

482x381x80 mm  
489x388x417 mm

#### Weight:

3600 gr  
18700 gr

#### Material Description

##### Toilet seat:

The material is colour ingrained duroplast (UF A 10 = urea formaldehyde) that contains no environmentally hazardous substances. The body consists of approx. 50% urea (NH<sub>2</sub>CONH<sub>2</sub>), approx. 25% cellulose and approx. 25% formaldehyde (HCHO), as well as small amounts of various fillers and additives.

##### Buffers:

EVA (copolymer made of ethylene and vinyl acetate).

##### Damper kit:

Hydraulic damper with plastic casing and metal shaft.  
Damper liquid: Silicone oil.

##### Mount/hinges:

Stainless steel ASTM A351 grade CF-8.

Composition: Chrome (cr) 18-21%, nickel (ni) 8-11%, carbon <0,08%, molybdenum, silicone, sulphur, titanium. Plastic Grivory GV-5H.

##### Konsol:

Acid proof stainless steel type EN 1.4404/A1S1 316L

Composition: Chrome (cr) 16,5-18,5%, nickel (ni) 10-13%, molybdenum 2-2,5% , mangan, silicium, sulphur, titanium.

#### Suitability List

Usable on D-shaped toilets - see [www.pressalit.com](http://www.pressalit.com)

#### Cleaning Instructions

Use a mild soap solution to clean the seat. Please take care that the seat and hinges are not left damp. Dry off any residual water or cleaning agent with a soft cloth. Avoid contact of the seat and hinges with abrasive, corrosive or chlorine-based cleaners, as these may cause damage or lead to flash rust. Therefore, when cleaning the bowl, make sure that the seat and cover are kept in an upright position until all cleaning agent has been flushed away.

The guarantee includes faults or defects in the material of our products within a period of 10 years.  
Products subject to minor technical modifications and design deviations E. & O.E.



Pressalit A/S, Denmark



[www.pressalit.com](http://www.pressalit.com)

European Sales Agencies  
Leith House, 39 Campion Drive  
Tanfield Lea, Stanley  
Co Durham, DH9 9PQ, United Kingdom  
T: +44 1207 236622  
F: +44 1207 236633  
[info@europeansalesagencies.com](mailto:info@europeansalesagencies.com)  
[www.europeansalesagencies.com](http://www.europeansalesagencies.com)

Pressalit A/S  
Pressalitvej 1  
8680 Ry, Denmark  
T: +45 8788 8788  
F: +45 8788 8789  
[pressalit@pressalit.com](mailto:pressalit@pressalit.com)  
[www.pressalit.com](http://www.pressalit.com)

**PRESSALIT®**  
seats